

Conservative Dentistry



Bassi Logic™

Next generation heat treatment for safety *and* efficiency.

- **Designed for Safety & Efficiency**

Next generation heat treatment retains sharpness with great flexibility.

- **Cuts Like Steel**

Completes instrumentation in a third less time than leading single file systems†.

- **Structure-Preserving Flexibility**

Significantly greater resistance to cyclic fatigue compared with other single file systems*.

- **Single-File Shaping Simplicity**

Bassi Logic™ can be used in reciprocating or continuous rotary motors.

- **Shaped to Clean**


Every file is designed with a specific helix that promotes the highest cutting efficiency.

- **Conservative Tapers**

No longer is flaring, brushing or straight line access needed.

30%
Faster Instrumentation


3.5x
Cyclic Fatigue Resistance



Clinical Case by Hugo Bastos, DDS



Clinical Case by Frederico Laperriere, DDS



†Brazilian Dental Journal (2016) 27(2): 217-222

*IEJ Iranian Endodontic Journal 2017;12(4): 468-473

Bassi Logic™ Conservative. Efficient. Advanced.

New Logic Handle

Taper Color
 01 White
 03 Yellow
 04 Red
 05 Blue
 06 Green
 08 Black
 10 White

Logic™ Glidepath
4 pack

.01 TAPER

SIZE	Cross Section	Speed	Torque
25/.01	Quadruple Helix Cross Section	350 RPM	1 Ncm
30/.01			
35/.01			
40/.01			
45/.01			
50/.01			

Logic™ Joker
4 pack

SIZE	Cross Section	Speed	Torque
15/.03	Square Cross Section	350-600 RPM	2 Ncm
15/.05	Square Cross Section	600-950 RPM	2 Ncm

Gutta-Percha Points
.03, .04, .05, .06 tapers
60 points

Logic™ Shaping
4 pack

SIZE	Cross Section	Speed	Torque
25/.03	Double Helix Cross Section	350-600 RPM	2 Ncm
30/.03			
35/.03			
40/.03			

.04 TAPER

SIZE	Cross Section	Speed	Torque
25/.04	Triple Helix Cross Section	600-950 RPM	2 Ncm

.05 TAPER

SIZE	Cross Section	Speed	Torque
25/.05	Double Helix Cross Section	600-950 RPM	4 Ncm
30/.05			
35/.05			
40/.05			

.06 TAPER

SIZE	Cross Section	Speed	Torque
25/.06	Double Helix Cross Section	600-950 RPM	4 Ncm

Bassi™
Gutta Percha Points
60 POINTS

Rx ONLY. DENTAL USE ONLY.
For instructions and reorders: BassiEndo.com or 800.234.0045

Gutta-Percha Points
Pack of 60 pcs.
Individual kit
25/03,30/03,35/03,40/03,25/04,
30/04,25/05,30/05,35/05,
40/05, 25/06

Assortment (10 each of 6 sizes)
25/03,30/03,35/03,25/05,
30/05,35/05

Logic™ Retreatment
3 pack/4 pack

SIZE	Cross Section	Speed	Torque
30/.10	Double Helix Cross Section	600-900 RPM	4 Ncm

.08 TAPER

SIZE	Cross Section	Speed	Torque
25/.08	Triple Helix Cross Section	600-900 RPM	4 Ncm

.06 TAPER

SIZE	Cross Section	Speed	Torque
20/.06	Triple Helix Cross Section	350 RPM	1.5 Ncm

Logic™ Resin Block
Practice blocks perfect for training
6 pack

Bassi™

+1 (407) 993-7100
800-234-0045 (USA)
BassiEndo.com
ref #: 012022

Logic™ Files are available in 21mm, 25mm & 31 mm.